

CPCI Power Backplane With P 47 Connector

Power Backplane for CompactPCI Applications. With P47 Power Connector.

FEATURES

In accordance with: PICMG 2.11 R1.0 CompactPCI Power Interface specification

In accordance with: PICMG 2.9 R1.0 System Management Bus specification

Single, parallel or redundant operation possible

Geographical address adjustable

Power supply over crimp contacts inserted into the plug, no supply voltage on the backplane

Power cable available as an accessory

DC outlets with powerbugs for extremely low drops in voltage



SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23098-393	Backplane	1	3U	CompactPCI Power Backplane with P47	8HP	
23098-396	Backplane	1	6U	CompactPCI Power Backplane with P47	8HP	
23098-395	Backplane	1	6U	CompactPCI Power Backplane with P47	8HP	
23098-394	Backplane	2	3U	CompactPCI Power Backplane with P47	8HP	P47

Table 2/2

Catalog Number	Power Connector Type	Utility Connector Type	Width	Package Quantity
23098-393	(1) P47	SMCQ, 12-pin, MicroMatch, 10-pin	39.6mm	1
23098-396	(2) P47	SMCQ, 12-pin, MicroMatch, 10-pin	39.6mm	1

Catalog Number	Power Connector Type	Utility Connector Type	Width	Package Quantity
23098-395	(1) P47	SMCQ, 12-pin, MicroMatch, 10-pin	39.6mm	1
23098-394	(2) P47	SMCQ, 12-pin, MicroMatch, 10-pin	80.3mm	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE