

# Straight Section Lay-in Painted Galvanized Hinged-Cover

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs.

## FEATURES

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs

**Color Code:** ANSI 61  
**Finish:** Galvanized; Powder Coated  
**Color:** Gray  
**Material:** Mild Steel

## SPECIFICATIONS

| Catalog Number | Article Number | Type             | Height | Width | Depth  | Thickness |
|----------------|----------------|------------------|--------|-------|--------|-----------|
| F66T3R60       | 43659          | Straight Section | 152mm  | 152mm | 1524mm | 1.52mm    |
| F66T3R120      | 43679          | Straight Section | 152mm  | 152mm | 3048mm | 1.52mm    |
| F66T3R12       | 43639          | Straight Section | 152mm  | 152mm | 305mm  | 1.52mm    |
| F44T3R60       | 43509          | Straight Section | 102mm  | 102mm | 1524mm | 1.52mm    |
| F44T3R120      | 43529          | Straight Section | 102mm  | 102mm | 3048mm | 1.52mm    |
| F44T3R12       | 43489          | Straight Section | 102mm  | 102mm | 305mm  | 1.52mm    |
| F88T3R60       | 43819          | Straight Section | 203mm  | 203mm | 1524mm | 1.9mm     |
| F88T3R120      | 43839          | Straight Section | 203mm  | 203mm | 3048mm | 1.9mm     |
| F88T3R12       | 43799          | Straight Section | 203mm  | 203mm | 305mm  | 1.9mm     |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**