

# nVent CADDY Ladder Tray Clip

The nVent CADDY Ladder Tray Clip makes attaching ladder trays to strut profiles quick and easy—featuring a single-piece design, ready for use out-of-the box with no loose hardware.

Offering two simple installation methods, the Ladder Tray Clip can be either installed on top of the strut or slid in from either end of the channel, increasing flexibility and giving contractors more options on the job. Designed for both indoor and outdoor installations, the hot-dip galvanized finish and hardware ensure longevity on rooftop, solar and trapeze projects.

## FEATURES

Single-piece design with hardware pre-installed to reduce components

Simple and time-saving; just drop and twist the Ladder Tray Clip directly into the strut profile

Works on ladder tray with up to ½ in flange thickness

Hot-dip galvanized clamp and hardware for demanding environments

Integrated clamping teeth for superior holding strength and load ratings



## SPECIFICATIONS

Table 1/2

| Catalog Number | Material | Finish             | Flange Thickness (FT) | A     | B       | Torque (TQ) |
|----------------|----------|--------------------|-----------------------|-------|---------|-------------|
| LTC            | Steel    | Hot-Dip Galvanized | 13 mm Max             | 49 mm | 38.1 mm | 41 N·m      |

Table 2/2

| Catalog Number | Ultimate Static Load 1 (F1) | Ultimate Static Load 2 (F2) | Ultimate Static Load 3 (F3) |
|----------------|-----------------------------|-----------------------------|-----------------------------|
| LTC            | 2225N                       | 3100N                       | 10675N                      |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

