# Rain Hoods, MSST

A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

## FEATURES

Description: To be fitted as extra protection on stainless steel enclosures. The roof is slightly sloped and has a dripstrip.

Material: 1.5 mm stainless steel AISI 304 / AISI 316L.

Finish: 400 pre-grained stainless steel.

**Thickness:** 1.5mm
**Finish:** Brushed

## SPECIFICATIONS

Table 1/2

| Catalog Number | Height | Width | Depth | Material | Product Family | Enclosure Material |
|---|---|---|---|---|---|---|
| MSST0650N-316 | 500mm | 600mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0640N-316 | 400mm | 600mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0860N | 600mm | 800mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1060N | 600mm | 1000mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST0850N-316 | 500mm | 800mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST1260N-316 | 600mm | 1200mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0650N | 500mm | 600mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1060N-316 | 600mm | 1000mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0850N | 500mm | 800mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1260N | 600mm | 1200mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1040N-316 | 400mm | 1000mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST1240N | 400mm | 1200mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |

| Catalog Number | Height | Width | Depth | Material | Product Family | Enclosure Material |
|---|---|---|---|---|---|---|
| MSST0840N-316 | 400mm | 800mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0840N | 400mm | 800mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1250N-316 | 500mm | 1200mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0660N | 600mm | 600mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1240N-316 | 400mm | 1200mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST0660N-316 | 600mm | 600mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST1250N | 500mm | 1200mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1050N | 500mm | 1000mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |

Table 2/2

| Catalog Number | Height | Width | Depth | Material | Product Family | Enclosure Material |
|---|---|---|---|---|---|---|
| MSST1640N | 400mm | 1600mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST0640N | 400mm | 600mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST1050N-316 | 500mm | 1000mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST1040N | 400mm | 1000mm | 72mm | Stainless Steel 304 | Free-Standing | Mild Steel |
| MSST0860N-316 | 600mm | 800mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |
| MSST1640N-316 | 400mm | 1600mm | 72mm | Stainless Steel 316 | Free-Standing | Mild Steel |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.