

# nVent LENTON Interlok Standard Grout-Fill Coupler, Plain



## FEATURES

Designed to splice the same diameter bars

Smaller bars can be installed into the over-sized cavity end if required

Over-sized cavity allows for greater field tolerance

Taper-threaded end helps prevent movement of the reinforcing bars and eliminate misalignment

Requires less grout than most competitive systems

**Material:** Cast Iron  
**Finish:** Plain  
**Packaging:** Standard



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter 1 (Ø1) | Diameter 2 (Ø2) |
|----------------|----------------|--------------------|----------------|--------------------|-----------------|-----------------|
| LK5            |                | 16 mm              | #5             | 15M                | 65 mm           | 48 mm           |
| LK16           |                | 16 mm              | #5             | 15M                | 59 mm           | 41 mm           |
| LK11           | 145605         | 36 mm              | #11            | 35M                | 80 mm           | 62 mm           |
| LK7            | 145585         | 22 mm              | #7             |                    | 65 mm           | 48 mm           |
| LK6            | 145580         | 20 mm              | #6             | 20M                | 65 mm           | 48 mm           |
| LK8            | 145590         | 25 mm              | #8             | 25M                | 68 mm           | 51 mm           |
| LK20           |                | 20 mm              | #6             | 20M                | 62 mm           | 45 mm           |
| LK9            | 145595         | 28 mm              | #9             | 30M                | 71 mm           | 54 mm           |
| LK25           |                | 25 mm              | #8             | 25M                | 68 mm           | 51 mm           |
| LK10           | 145600         | 32 mm              | #10            |                    | 76 mm           | 59 mm           |


| Catalog Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter 1 (Ø1) | Diameter 2 (Ø2) |
|----------------|----------------|--------------------|----------------|--------------------|-----------------|-----------------|
| LK12           |                | 38 mm              |                |                    | 94 mm           | 70 mm           |
| LK36           |                | 36 mm              | #11            | 35M                | 81 mm           | 62 mm           |
| LKT14          | 145611         | 43 mm              | #14            | 45M                | 94 mm           | 70 mm           |
| LK40           |                | 40 mm              |                |                    | 94 mm           | 70 mm           |

| Table 2/2      |                |               |               |                |             |                  |                              |
|----------------|----------------|---------------|---------------|----------------|-------------|------------------|------------------------------|
| Catalog Number | Article Number | Length 1 (L1) | Length 2 (L2) | Bar Depth (BD) | Unit Weight | Package Quantity | Certifications               |
| LK5            |                | 200 mm        | 156 mm        | 22mm           | 1.98 kg     | 12               |                              |
| LK16           |                | 201 mm        | 168 mm        | 24mm           | 1.69 kg     | 110              | IAPMO®-UES, LA City Approval |
| LK11           | 145605         | 305 mm        | 251 mm        | 43mm           | 3.63 kg     | 1                | IAPMO®-UES, LA City Approval |
| LK7            | 145585         | 200 mm        | 156 mm        | 32mm           | 1.94 kg     | 1                | LA City Approval, IAPMO®-UES |
| LK6            | 145580         | 200 mm        | 156 mm        | 28mm           | 1.96 kg     | 12               | IAPMO®-UES, LA City Approval |
| LK8            | 145590         | 219 mm        | 178 mm        | 34mm           | 2.15 kg     | 8                | IAPMO®-UES, LA City Approval |
| LK20           |                | 226 mm        | 178 mm        | 35mm           | 1.98 kg     | 12               | IAPMO®-UES, LA City Approval |
| LK9            | 145595         | 248 mm        | 203 mm        | 38mm           | 2.44 kg     | 8                | LA City Approval, IAPMO®-UES |
| LK25           |                | 228 mm        | 178 mm        | 40mm           | 2.26 kg     | 8                |                              |
| LK10           | 145600         | 275 mm        | 229 mm        | 40mm           | 2.84 kg     | 8                | LA City Approval, IAPMO®-UES |
| LK12           |                | 386 mm        | 324 mm        | 44mm           | 7.14 kg     | 4                |                              |
| LK36           |                | 313 mm        | 251 mm        | 52mm           | 4.04 kg     | 8                |                              |
| LKT14          | 145611         | 386 mm        | 324 mm        | 56mm           | 7.26 kg     | 4                | IAPMO®-UES, LA City Approval |
| LK40           |                | 386 mm        | 324 mm        | 57mm           | 6.33 kg     | 4                |                              |

## ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE