

# Telescopic Slides C-Profile for Cabinet



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

## FEATURES

For mounting 84 HP wide sub racks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the sub rack (it is inserted into the guiding profile like a telescopic slide)

**Material:** Aluminum  
**Finish:** Anodized  
**Type:** C Profile  
**Product Type:** Telescopic Slide



## SPECIFICATIONS

| Catalog Number | Depth  | Package Quantity |
|----------------|--------|------------------|
| 24562-446      | 250mm  | 2                |
| 24562-474      | 800mm  | 2                |
| 24562-460      | 500mm  | 2                |
| 24562-461      | 600mm  | 2                |
| 24562-473      | 1200mm | 2                |
| 24562-464      | 600mm  | 2                |
| 24562-452      | 900mm  | 2                |
| 24562-466      | 800mm  | 2                |
| 24562-451      | 800mm  | 2                |
| 24562-467      | 900mm  | 2                |
| 24562-468      | 1000mm | 2                |
| 24562-449      | 600mm  | 2                |

| Catalog Number | Depth  | Package Quantity |
|----------------|--------|------------------|
| 24562-472      | 1100mm | 2                |

## ADDITIONAL PRODUCT DETAILS

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**