

Easy Swap Adaptor Plenums for Air Conditioners



When existing air conditioners are damaged or have reached end-of-life, Easy Swap Adaptor Plenums provide a quick and easy means for attaching a new nVent HOFFMAN air conditioners to the cutout left on the enclosure.

INDUSTRY STANDARDS

Maintains NEMA Type 12 rating when properly installed on a Type 12 enclosure.

NEMA Type 12

IP 54

FEATURES

No modification of the enclosure required - designed to match the enclosure cut-out and mounting holes of the air conditioner being replaced

Plenum design allows for optimum air flow (vs. a flat plate that can block the air intake and air outtake left by the older air conditioner)

Gasket included

Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLM28G28	26294	NEMA Type 12	EasySwap	724mm	432mm	38mm
PLM33N28	26296	NEMA Type 12	EasySwap	871mm	305mm	38mm
PLRG52	19862	NEMA Type 12	EasySwap	1553mm	435mm	38mm
PLKG28	26582	NEMA Type 12	EasySwap	937mm	486mm	38mm
PLCR23N21		NEMA Type 12	EasySwap	584mm	254mm	38mm
PLM36N36	26297	NEMA Type 12	EasySwap	984mm	381mm	38mm
PLKG52	26581	NEMA Type 12	EasySwap	1335mm	486mm	38mm

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLRG57	26073	NEMA Type 12	EasySwap	1553mm	530mm	38mm
PLM28N17	26557	NEMA Type 12	EasySwap	724mm	432mm	38mm
PL17N21SS		NEMA Type 12	EasySwap	530mm	305mm	38mm
PLRG28	21496	NEMA Type 12	EasySwap	950mm	431mm	38mm
PLM52G52	26298	NEMA Type 12	EasySwap	1335mm	433mm	38mm
PLRN28	26068	NEMA Type 12	EasySwap	737mm	292mm	38mm
PLR2N17	26067	NEMA Type 12	EasySwap	550mm	305mm	38mm
PLHC52T53	26302	NEMA Type 12	EasySwap	1342mm	584mm	38mm
PLKTN17	26568	NEMA Type 12	EasySwap	483mm	305mm	38mm
PLM13N17	26556	NEMA Type 12	EasySwap	448mm	362mm	38mm
PLT29G28	26295	NEMA Type 12	EasySwap	724mm	432mm	38mm
PLHC52G57	26301	NEMA Type 12	EasySwap	1463mm	583mm	38mm
PLKTN28	26505	NEMA Type 12	EasySwap	845mm	311mm	38mm

Table 2/2

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLR1N17	26066	NEMA Type 12	EasySwap	550mm	330mm	38mm
PLM13N16		NEMA Type 12	EasySwap	448mm	362mm	67mm
PLR2G28	26504	NEMA Type 12	EasySwap	950mm	431mm	38mm
PLRN36	26538	NEMA Type 12	EasySwap	965mm	400mm	38mm
PLPN36	26537	NEMA Type 12	EasySwap	927mm	305mm	38mm
PL17N21		NEMA Type 12	EasySwap	530mm	305mm	38mm
PLCR23N21SS		NEMA Type 12	EasySwap	584mm	254mm	38mm

ADDITIONAL PRODUCT DETAILS

To quickly identify the correct air conditioner and plenum download the spec sheet from the Downloads tab or download the Easy Swap app from Apple App or Google play stores

Please contact Customer Service for support in finding an appropriate cross for older HOFFMAN/Mclean models not shown above.

Prior to ordering, ensure Adaptor Plenum dimensions do not exceed available space on the enclosure mounting surface.

ISC is a registered trademark of ISC Sales, Inc.

Kooltronic is a registered trademark of Kooltronic, Inc.

Pfannenbergl is a registered trademark of Pfannenbergl Incorporated

Rittal is a registered trademark of Rittal Corporation

Adaptor Plenums for Rittal are not suitable for replacing partial-recessed or fully-recessed mounted air conditioners.

Thermal Edge is a registered trademark of Thermal Edge, Inc.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE