

Universal U-Connector Galvanized

Galvanized U-Connectors are used to rigidly join lay-in wireway straight sections in series, as well as straight sections to fittings. The U-connector top swings aside to retain the lay-in feature of the wireway solution.

FEATURES

Galvanized U-Connectors are used to rigidly join lay-in wireway straight sections in series, as well as straight sections to fittings

Top swings aside to retain the lay-in feature

U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates, or reducers

F44GUCGV and F66GUCGV designed to accept new Snap Connect Wireway for ease-of-installation; backwards compatible with legacy wireway design

Finish: Galvanized
Material: Mild Steel

SPECIFICATIONS

Catalog Number	Article Number	Type	Height	Width	Thickness
F66GUCGV	88620	U-Connector	152mm	152mm	1.52mm
F44GUCGV	88330	U-Connector	102mm	102mm	1.52mm
F22GUCGV	88060	U-Connector	64mm	64mm	1.52mm
F88GUCGV	88840	U-Connector	203mm	203mm	1.9mm
F1010GUCGV	57170	U-Connector	254mm	254mm	1.9mm
F1212GUCGV	89040	U-Connector	305mm	305mm	1.9mm

ADDITIONAL PRODUCT DETAILS

Note: with presence of extruded holes, electric drivers recommended to secure fasteners

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE