

RatiopacPRO/-AIR Strap Handle

Strap handle for RatiopacPRO/-AIR with a static load-carrying capacity of 20 kg. Retrofittable without mechanical tooling on case.

FEATURES

Static load-carrying capacity 20 kg

Retrofittable without mechanical tooling on the case side panel

Works With: Cases
Product Type: Handle
Product Family: RatiopacPRO; RatiopacPRO AIR



SPECIFICATIONS

Catalog Number	Rack Height	Depth	Package Quantity	Handle Type
24571-308	3U	315mm	1	Strap
24571-316	4U	435mm	1	Strap
24571-315	4U	375mm	1	Strap
24571-314	4U	315mm	1	Strap
24571-309	3U	375mm	1	Strap
24571-310	3U	435mm	1	Strap

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE