VME64x System, 2 U, 4 Slot, Pluggable PSU



CATALOG NUMBER

20836-245

VME64x system for 4 horizontally mounted VME64x boards 6 U, 160 mm. Rear I/ O option. The power for the system is supplied by up to two pluggable power supplies. A hot swap fan tray with 4 fans guarantee an excellent cooling.

FEATURES

System in accordance with IEC 60297-3-101, 102, 103; IEEE 1101.1, 1101.10/11; backplane conforms to VITA 1.1-1997

Power backplane to PICMG 2.11 (P 47), prepared for installation of two 19" compatible PSUs, 300 W (3 U, 8 HP)

Heat dissipation by a fan tray with 2 fans, cooling from right to left side; fan monitoring and voltage display

System for horizontal board mounting with board formats; Front: 6 U, 160 mm deep; Rear, rear I/O: 6 U, 80 mm deep

PRODUCT ATTRIBUTES

Product Type: System
Number of Slots: 4
Type: 19" Rack Mount
Backplane Type: 6 U VME64 Extension
Data Transfer: VME64; VME2eSST
Power per Slot: 30W
Input Voltage AC: 100 – 240V
Airflow Direction: Left to Right
Rack Height: 2U
Power Supply Type: (2) Pluggable PSU
Power Supply Included: No
Rear I/O: Yes
Complies With: ANSI/VITA 1.1-1997

Depth: 277.5mm

Height: 88.1mm

Width: 449mm

Net Weight: 8.35kg

Package Quantity: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.