

# Glazed Doors, DNG



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

## FEATURES

Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

**Thickness:** 2mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Window Size  | Product Family |
|----------------|----------------|--------|-------|-------|--------------|----------------|
| DNG2008R5      | DNG2008R5      | 1982mm | 793mm | 17mm  | 1776 x 615mm | Free-Standing  |
| DNG1408R5      | DNG1408R5      | 1382mm | 793mm | 17mm  | 1176 x 615mm | Free-Standing  |
| DNG2006R5      | DNG2006R5      | 1982mm | 593mm | 17mm  | 1776 x 415mm | Free-Standing  |
| DNG1106R5      | DNG1106R5      | 1082mm | 593mm | 17mm  | 876 x 415mm  | Free-Standing  |
| DNG1206R5      | DNG1206R5      | 1182mm | 593mm | 17mm  | 976 x 415mm  | Free-Standing  |

| Catalog Number | Article Number | Height | Width | Depth | Window Size  | Product Family |
|----------------|----------------|--------|-------|-------|--------------|----------------|
| DNG1806R5      | DNG1806R5      | 1782mm | 593mm | 17mm  | 1576 x 415mm | Free-Standing  |
| DNG1608R5      | DNG1608R5      | 1582mm | 793mm | 17mm  | 1376 x 615mm | Free-Standing  |
| DNG1406R5      | DNG1406R5      | 1382mm | 593mm | 17mm  | 1176 x 415mm | Free-Standing  |
| DNG2208R5      | DNG2208R5      | 2182mm | 793mm | 17mm  | 1976 x 615mm | Free-Standing  |
| DNG1208R5      | DNG1208R5      | 1182mm | 793mm | 17mm  | 976 x 615mm  | Free-Standing  |
| DNG1808R5      | DNG1808R5      | 1782mm | 793mm | 17mm  | 1576 x 615mm | Free-Standing  |
| DNG2206R5      | DNG2206R5      | 2182mm | 593mm | 17mm  | 1976 x 415mm | Free-Standing  |
| DNG1606R5      | DNG1606R5      | 1582mm | 593mm | 17mm  | 1376 x 415mm | Free-Standing  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**