

# Lifting Eye Bolts, LE

These lifting eyes guarantee safe transportation and handling of the enclosure.

## FEATURES

Description: Mounts directly to the frame corner pieces of the enclosure for when lifting operations are required. Complies with DIN 580 lifting requirements. M12 thread.

Maximum load: 3400N per lifting eye with max angle of 45°. Please follow nVent HOFFMAN lifting instructions.

Pack quantity: 4 pieces.



## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Material             | Finish      |
|----------------|----------------|--------|-------|-------|----------------------|-------------|
| LE9304         | LE9304         | 71mm   | 50mm  | 30mm  | Mild Steel           | Zinc Plated |
| LE9304SS       | LE9304SS       | 71mm   | 50mm  | 30mm  | Stainless Steel 304  | Mill        |
| LE9316SS       |                | 71mm   | 50mm  | 30mm  | Stainless Steel 316L | Mill        |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.