

nVent CADDY Self-Cutting Cable Tie



The nVent CADDY Self-Cutting Cable Tie is a versatile, tool-free datacom solution for bundling large amounts of cables. This simple, yet innovative product features a built-in cutting blade to ensure a secure fastening and a safe, clean tie-off finish. Made from durable 6/6 nylon, the Self-Cutting Cable Tie boasts a robust 50lb/ 22Kg of tensile strength.

FEATURES

Eliminates sharp edges and protects exposed skin from cuts during installation

Lock and twist to cut, no cutting tools required

Different colors including a black UV-protected version to meet specific needs

RoHS (Restriction of Hazardous Substances Directive) compliant

Halogen free

cULus Listed to UL 62275/CSA C22.2 No. 62275, UL Certified to IEC 62275

Complies With: IEC® 60695-2-11 (Glow Wire Test 960 °C)




SPECIFICATIONS

Catalog Number	Article Number	Material	Color	Length (L)	Width (W)	Installation Temperature	Operating Temperature
CADTIESC14CBAP	601009	Nylon, Stainless Steel 301 (EN 1.4310)	Black	355.6m m	4.32 mm	0 °C Min	-20 to 85 °C
CADTIESC8CBAP	601018	Nylon, Stainless Steel 301 (EN 1.4310)	Black	203.2m m	4.32 mm	0 °C Min	-20 to 85 °C
CADTIESC8CNAP	601019	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	203.2m m	4.32 mm	0 °C Min	-20 to 85 °C
CADTIESC11CBAP	601000	Nylon, Stainless Steel 301 (EN 1.4310)	Black	279.4m m	4.32 mm	0 °C Min	-20 to 85 °C

Catalog Number	Article Number	Material	Color	Length (L)	Width (W)	Installation Temperature	Operating Temperature
CADTIESC11CNAP	601001	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	279.4m	4.32 mm	0 °C Min	-20 to 85 °C
CADTIESC14CNAP	601010	Nylon, Stainless Steel 301 (EN 1.4310)	Natural	355.6m	4.32 mm	0 °C Min	-20 to 85 °C

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

