nVent | CADDY

We connect and protect

FCS Height Adjustable Loop Hanger, 1 1/2" Pipe, 40 DN, 48 mm OD, M8 Rod

CATALOG NUMBER

FCS0150M8

FEATURES

- Recommended for the suspension of stationary non-insulated fire sprinkler pipe
- Redesigned strap and cup nut minimize friction for easier adjustment up and down the threaded rod (1/2" to 4" sizes)
- Formed tips on the upper strap simplify disassembly and reassembly of the hanger
- Rolled edges on the strap help to guide the pipe through, limiting binding and damage to metal or plastic pipe
- Package includes all necessary hardware for installation

VdS

PRODUCT ATTRIBUTES

- Article Number: 597965
- Material: Steel
- Finish: Electrogalvanized
- Pipe Size: 1 1/2"
- NB/DN: 40
- Outer Diameter (OD): 48 mm
- Rod Size (RS): M8
- Width (W): 10 mm
- A: 97 mm
- B: 41 mm
- C: 17 mm
- Static Load: 2000N
- Wrench Size: 13 mm

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.