

Copper Utility Ground Plate



The Copper Utility Ground Plate is designed to create an equipotential plane and help protect personnel and valuable equipment. This is particularly important in the utility industry, where safety is a top priority. The plate's large surface area helps to dissipate current into the ground, reducing the risk of electrical shock and equipment damage. Additionally, the plate is available with a pigtail configuration, making it a versatile solution for various applications within the irrigation industry.


FEATURES

Provides a large surface area to dissipate current into the ground

Lays flat underground and can attach the pigtail via a ground rod

SPECIFICATIONS

Catalog Number	Connector	Length (L)	Width (W)	Thickness (T)
UGP719SBP5	ESB2 Split Bolt	489mm	191 mm	1.59 mm
UGP738SBP5	ESB2 Split Bolt	978mm	191 mm	1.59 mm
UGP738	SRGC46	978mm	191 mm	1.59 mm
UGP719	SRGC46	489mm	191 mm	1.59 mm
UGP738P5	SRGC46	978mm	191 mm	1.59 mm
UGP719BP5	SRGC46	489mm	191 mm	1.59 mm
UGP738P10	SRGC46	978mm	191 mm	1.59 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE