Rooftop Pyramid H-Frame Post Base, Foam

CATALOG NUMBER

PHB

FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Mounting hardware pre-installed in bases
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels

PRODUCT ATTRIBUTES

Article Number: 360422
Material: Steel;Polypropylene;Polyethylene
Finish: Hot-Dip Galvanized
Temperature: -34 to 54.4 °C
Static Load Safety Factor: 3:1
Rooftop Interface: Foam
Strut Type: A (41 x 41 mm)
Height (H): 117 mm
Length (L): 314mm
Width (W): 314 mm
Surface Area: 0.09m²
Unit Weight: 1.8 kg
Static Load: 3335N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.