

# nVent CADDY Pyramid ST Adjustable Strut Support



## FEATURES

Height adjustability provides effective navigation of pipe, conduit, duct and cable tray around obstructions

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance

|                                   |                                  |
|-----------------------------------|----------------------------------|
| <b>Static Load Safety Factor:</b> | 3:1                              |
| <b>Temperature:</b>               | -45 to 65 °C                     |
| <b>Finish:</b>                    | Hot-Dip Galvanized               |
| <b>Material:</b>                  | Polyethylene;Polypropylene;Steel |



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Length 1 (L1) | Length 2 (L2) | Height (H)   | Width (W) | Surface Area         |
|----------------|----------------|---------------|---------------|--------------|-----------|----------------------|
| PSA10CH13      | 360468         | 254 mm        | 317.5 mm      | 152 - 330 mm | 203 mm    | 59355mm <sup>2</sup> |
| PSA16AH18      | 360469         | 406 mm        | 483 mm        | 178 - 457 mm | 203 mm    | 91613mm <sup>2</sup> |

Table 2/2

| Catalog Number | Article Number | Unit Weight | Static Load |
|----------------|----------------|-------------|-------------|
| PSA10CH13      | 360468         | 2 kg        | 4450N       |
| PSA16AH18      | 360469         | 3 kg        | 6670N       |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

