

# Telescoping Pipe Stand



The nVent CADDY Telescoping Pipe Stand is an adjustable and flexible solution for supporting horizontal pipe runs using a traditional V-Saddle or bolt flange attachment method. The design ensures a faster installation that quickly adapts to a variety of pipe sizes and heights from the floor. The unique V-bolt fastener—with built in nVent CADDY Rod Lock Technology and flange attachment tabs—can adapt to a large range of bolt patterns, sizes and pipe diameters, ultimately reducing inventory and the amount of components needed with over two-thirds savings. Offering a complete out-of-the-box assembly, the nVent CADDY Telescoping Pipe Stand is a contemporary solution for pipe runs.

## FEATURES

Supports and fastens low-to-the-ground horizontal pipe runs

Telescoping post provides fast vertical height adjustment

Designed to minimize fabrication and reduce installation time of a complete stand compared to traditional methods

Integrated weep hole at bottom of stand provides drainage for condensation

Includes four holes for anchoring base to floor

Conforms with Federal Specification WW-H-171 (Type 36, 37, 38, 39), Manufacturers Standardization Society ANSI/MSS SP-58 (Type 36, 37, 38)

**Finish:** Electrogalvanized

**Material:** Steel

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | NB/DN     | A             | B      | C      | D      |
|----------------|----------------|-----------|---------------|--------|--------|--------|
| CTS10          | 580066         | 125 - 250 | 605 - 1070 mm | 365 mm | 216 mm | 165 mm |
| CTSS10         |                | 125 - 250 | 410 - 655 mm  | 365 mm | 216 mm | 165 mm |
| CTS10A24       |                | 300 - 600 |               | 686 mm |        |        |

Table 2/2

| Catalog Number | Article Number | E            | G             | Hole Size (HS) | Static Load | Unit Weight |
|----------------|----------------|--------------|---------------|----------------|-------------|-------------|
| CTS10          | 580066         | 135 - 260 mm | 608 - 1021 mm | 16 mm          | 13540N      | 16.1 kg     |
| CTSS10         |                | 135 - 260 mm | 405 - 595 mm  | 16 mm          | 13540N      | 14.3 kg     |
| CTS10A24       |                |              |               | 16 mm          |             | 3.4 kg      |





## ADDITIONAL PRODUCT DETAILS

When insulating pipe install V-bolt after insulation.

Telescoping pipe stand can accommodate pipes up to 24" when v-bolt is removed. Installer must determine weight of the pipe and proper spacing when supporting larger sizes.

2:1 safety factor used for metric Static Load. 3.5:1 safety factor used for imperial Static Load.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

