We connect and protect

nVent CADDY Speed Link SLK with Hook, 2 mm Wire, 3 m Length

CATALOG NUMBER

SLK2L3R2

FEATURES

- Complete system includes wire, locking device and pre-assembled hook end fitting
- Hooks to a wide range of nVent CADDY fasteners
- Fastens to the building structure or hanging services by looping around and hooking to wire rope
- Easy to remove for applications requiring maintenance
- Spring latch helps provide secure connection
- Insert cable through hole and use bottom side of hook as an end stop
- Also available in Y-hook configuration

PRODUCT ATTRIBUTES

Article Number: 196620
Material: Steel;Polypropylene;Zinc Alloy
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Wire Rope Diameter: 2 mm
Complies With: SMACNA HVAC-DCS
Wire Rope Length: 3m
A: 57 mm
B: 22 mm
C: 5.5 mm
Height (H): 55 mm
Width (W): 19 mm

Thickness (T): 12.5 mm

Angle (a): 90 ° Max

Static Load: 440N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.