We connect and protect

Improved Cat HP J-Hook with Hammer-On Flange Clip, Swivel, 50mm dia,8–14mmFlange

CATALOG NUMBER

CAT32HP58

The Improved nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip, Swivel is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Hammer-On Flange Clip, Swivel attachment. With a 360-degree rotation, this solution supports flexible cable routing, while rounded edges maintain proper bend radius for high-performance data cables including Cat 5e through Cat 7 and fiber optic. Installers can simplify setup and improve productivity by eliminating screws, rivets, and special tools. Engineered for strength and efficiency, the Assembly delivers superior fill capacity and securely clips onto beam flanges.

FEATURES

- Requires only a hammer to install
- Rotates 360 degrees to support various directional runs of cable
- Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications
- Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs
- Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic
- Complies with EN 50174-2
- Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

PRODUCT ATTRIBUTES

- Article Number: 181002
- Material: Steel;Spring Steel
- Finish: Pregalvanized;nVent CADDY Armour
- Diameter: 50 mm

Area: 2561mm²

Cable Capacity, Cat 5e: 90

Cable Capacity, Cat 6: 60

Cable Capacity, Cat 6A: 35

Flange Thickness: 8 - 14 mm

Static Load: 270N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.