Top And Bottom Panels For Floor Standing Enclosures, DPC

Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted.

FEATURES

Description: Required to cover the remaining space at the top and bottom. Used in combination with horizontal dividers CDH/CDHK, partial doors DP, partial panels DPP and cable space door DPA.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44. For IP 21 delivered without gasket.

Mounting requirements: DPC covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPC is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: Top and bottom panel with mounting accessories.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035
Thickness: 1.75mm

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPC0714R5	104mm	400mm	17mm	Free-Standing	Mild Steel

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPC0716R5	104mm	600mm	17mm	Free-Standing	Mild Steel
DPC0718R5	104mm	800mm	17mm	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.