We connect and protect

Wire Basket Tray Bar Splice Kit Electrogalvanized

CATALOG NUMBER

WBTBSPLICEKIT

The nVent CADDY Wire Basket Tray Bar Splice offers a versatile solution for straight sections and fittings within shaped wire basket tray systems. Engineered for structural continuity, the Bar Splice delivers enhanced support between tray runs. With a slotted design, contractors can create innovative field configurations—ideal for forming reducers or achieving precise angles. Whether you're adapting tray geometry or reinforcing connections, the Bar Splice ensures a clean, secure fit with finishes that match your installation.

FEATURES

- Multiple color options to coordinate with cable tray selection
- Creates additional support for cable tray runs
- Optimal for angles 30 degrees and smaller

PRODUCT ATTRIBUTES

Material: Steel
Finish: Electrogalvanized
Height (H): 17.46 mm
Width (W): 4.55 mm
Length (L): 304.8mm
Unit Weight: 0.127 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.