

Threaded Rod

FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

Quality Class: 4.8
Finish: Electrogalvanized
Material: Steel

SPECIFICATIONS

Catalog Number	Article Number	Rod Size (RS)	Length (L)	Static Load
050M103000	592670	M10	3000mm	7000N
050M63000	592650	M6	3000mm	2400N
050M123000	592680	M12	3000mm	10000N

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

