

# T-Grid Fan/Fixture Mount

## FEATURES

2-1/8" electrical box is premounted and centered on bracket and is fully adjustable up to 8" in either direction

Electrical box has three open knockouts for quick installation

Each kit includes screws to mount fan, nVent CADDY Speed Link to support from building structure and two Fixture Mount Stabilizer Clips (FMSBC1) to stabilize ceiling tiles

**Finish:** Pregalvanized  
**Material:** Steel



## SPECIFICATIONS

| Catalog Number | Working Load | T-Grid Span |
|----------------|--------------|-------------|
| 512HDFM35      | 150N         | 609.6mm     |
| 512HDFM70      | 300N         | 609.6mm     |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

