

Mesh Bonding Network Connector, MBNC240A



FEATURES

Allows for fast, simple and economical field connection of grounding and bonding wires


Heavy duty clamps with stainless steel hardware are suitable for direct burial

Can be combined with Universal Pedestal Clamp for bonding to various pedestal sizes for mesh bonding networks



SPECIFICATIONS

Catalog Number	Material	Conductor Size
MBNC240A	Copper, Stainless Steel 304 (EN 1.4301)	#2 Solid - 4/0 Stranded, 35 mm ² - 100 mm ²



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE