122-Ti/T Rod to Z Purlin Clip



FEATURES


- Hammer-on clip compensates for angle of purlin
- Provides method for attaching rod to purlin


Material: Spring Steel
Finish: nVent CADDY Armour

SPECIFICATIONS

Catalog Number	Article Number	Thread Size (TS)	Flange Thickness (FT)	B	Static Load
122M10TI	175070	M10	2.8 mm Max	15 mm Min	450N
122M6TI	174890	M6	2.8 mm Max	15 mm Min	450N
122M8TI	174980	M8	2.8 mm Max	15 mm Min	450N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.