

Collar Screw, Knurled Head Short Version



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

FEATURES

For assembly of partial width front panels

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

Works With: Front Panels
Type: Screw
Product Type: Screw



SPECIFICATIONS

Table 1/2

Catalog Number	Length	Material	Finish	Package Quantity	Thread Size	Depth
21101-749	12.3mm	Brass, Lead Free	Nickel Plated	100	M2.5	18.3mm
21101-106	11mm	Steel			M2.5	
21100-268	11mm	Brass	Nickel Plated	100	M2.5	

Table 2/2

Catalog Number	Height	Width	Torque	Certifications
21101-749	8mm	8mm	0.3N·m	RoHS
21101-106				
21100-268				

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE