

# Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

## FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

## SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Height | Width | Depth | Door Type  | Product Family |
|----------------|----------------|--------|-------|-------|------------|----------------|
| DN2006RR5      | DN2006RR5      | 1982mm | 593mm | 17mm  | Right Door | Free-Standing  |

| Catalog Number | Article Number | Height | Width | Depth | Door Type  | Product Family |
|----------------|----------------|--------|-------|-------|------------|----------------|
| DN1206R5       |                | 1182mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN1810R5       | DN1810R5       | 1782mm | 993mm | 17mm  | Plain      | Free-Standing  |
| DN1610R5       | DN1610R5       | 1582mm | 993mm | 17mm  | Plain      | Free-Standing  |
| DN2205RR5      | DN2205RR5      | 2182mm | 493mm | 17mm  | Right Door | Free-Standing  |
| DN2008LR5      | DN2008LR5      | 1982mm | 793mm | 17mm  | Left Door  | Free-Standing  |
| DN2208R5       | DN2208R5       | 2182mm | 793mm | 17mm  | Plain      | Free-Standing  |
| DN1608R5       | DN1608R5       | 1582mm | 793mm | 17mm  | Plain      | Free-Standing  |
| DN2004LR5      | DN2004LR5      | 1982mm | 393mm | 17mm  | Left Door  | Free-Standing  |
| DN1606RR5      | DN1606RR5      | 1582mm | 593mm | 17mm  | Right Door | Free-Standing  |
| DN1206RR5      |                | 1182mm | 593mm | 17mm  | Right Door | Free-Standing  |
| DN2004RR5      | DN2004RR5      | 1982mm | 393mm | 17mm  | Right Door | Free-Standing  |
| DN1606R5       | DN1606R5       | 1582mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN1804R5       |                | 1782mm | 393mm | 17mm  | Plain      | Free-Standing  |
| DN1606LR5      | DN1606LR5      | 1582mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN2005LR5      | DN2005LR5      | 1982mm | 493mm | 17mm  | Left Door  | Free-Standing  |
| DN1806R5       | DN1806R5       | 1782mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN1408R5       | DN1408R5       | 1382mm | 793mm | 17mm  | Plain      | Free-Standing  |
| DN2005R5       | DN2005R5       | 1982mm | 493mm | 17mm  | Plain      | Free-Standing  |
| DN1208R5       |                | 1182mm | 793mm | 17mm  | Plain      | Free-Standing  |

Table 2/3

| Catalog Number | Article Number | Height | Width | Depth | Door Type  | Product Family |
|----------------|----------------|--------|-------|-------|------------|----------------|
| DN2205LR5      | DN2205LR5      | 2182mm | 493mm | 17mm  | Left Door  | Free-Standing  |
| DN1406RR5      |                | 1382mm | 793mm | 17mm  | Right Door | Free-Standing  |
| DN2204R5       |                | 2182mm | 393mm | 17mm  | Plain      | Free-Standing  |
| DN2005RR5      | DN2005RR5      | 1982mm | 493mm | 17mm  | Right Door | Free-Standing  |
| DN2004R5       |                | 1982mm | 393mm | 17mm  | Plain      | Free-Standing  |
| DN1406R5       | DN1406R5       | 1382mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN2010R5       | DN2010R5       | 1982mm | 993mm | 17mm  | Plain      | Free-Standing  |
| DN1405LR5      |                | 1382mm | 493mm | 17mm  | Left Door  | Free-Standing  |
| DN1406LR5      |                | 1382mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN2006LR5      | DN2006LR5      | 1982mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN2006R5       | DN2006R5       | 1982mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN1405RR5      |                | 1382mm | 493mm | 17mm  | Right Door | Free-Standing  |
| DN2206R5       | DN2206R5       | 2182mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN1806LR5      | DN1806LR5      | 1782mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN1805LR5      | DN1805LR5      | 1782mm | 493mm | 17mm  | Left Door  | Free-Standing  |

| Catalog Number | Article Number | Height | Width | Depth | Door Type  | Product Family |
|----------------|----------------|--------|-------|-------|------------|----------------|
| DN1805R5       | DN1805R5       | 1782mm | 493mm | 17mm  | Plain      | Free-Standing  |
| DN1808R5       | DN1808R5       | 1782mm | 793mm | 17mm  | Plain      | Free-Standing  |
| DN1806RR5      | DN1806RR5      | 1782mm | 593mm | 17mm  | Right Door | Free-Standing  |
| DN1106R5       |                | 1082mm | 593mm | 17mm  | Plain      | Free-Standing  |
| DN2206RR5      | DN2206RR5      | 2182mm | 593mm | 17mm  | Right Door | Free-Standing  |

Table 3/3

| Catalog Number | Article Number | Height | Width | Depth | Door Type  | Product Family |
|----------------|----------------|--------|-------|-------|------------|----------------|
| DN1206LR5      |                | 1182mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN2210R5       |                | 2182mm | 993mm | 17mm  | Plain      | Free-Standing  |
| DN2008R5       | DN2008R5       | 1982mm | 793mm | 17mm  | Plain      | Free-Standing  |
| DN1804RR5      | DN1804RR5      | 1782mm | 393mm | 17mm  | Right Door | Free-Standing  |
| DN2206LR5      | DN2206LR5      | 2182mm | 593mm | 17mm  | Left Door  | Free-Standing  |
| DN1808RR5      | DN1808RR5      | 1782mm | 793mm | 17mm  | Right Door | Free-Standing  |
| DN1805RR5      | DN1805RR5      | 1782mm | 493mm | 17mm  | Right Door | Free-Standing  |
| DN1808LR5      | DN1808LR5      | 1782mm | 793mm | 17mm  | Left Door  | Free-Standing  |
| DN1804LR5      | DN1804LR5      | 1782mm | 393mm | 17mm  | Left Door  | Free-Standing  |
| DN2008RR5      | DN2008RR5      | 1982mm | 793mm | 17mm  | Right Door | Free-Standing  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**