

# nVent CADDY Self-Cutting Cable Tie



The nVent CADDY Self-Cutting Cable Tie is a versatile, tool-free datacom solution for bundling large amounts of cables. This simple, yet innovative product features a built-in cutting blade to ensure a secure fastening and a safe, clean tie-off finish. Made from durable 6/6 nylon, the Self-Cutting Cable Tie boasts a robust 50lb/ 22Kg of tensile strength.

## FEATURES

Eliminates sharp edges and protects exposed skin from cuts during installation

Lock and twist to cut, no cutting tools required

Different colors including a black UV-protected version to meet specific needs

RoHS (Restriction of Hazardous Substances Directive) compliant

Halogen free

cULus Listed to UL 62275/CSA C22.2 No. 62275, UL Certified to IEC 62275

**Complies With:** IEC® 60695-2-11 (Glow Wire Test 960 °C)



## SPECIFICATIONS

| Catalog Number | Article Number | Material                               | Color   | Length (L)  | Width (W)  | Installation Temperature | Operating Temperature |
|----------------|----------------|----------------------------------------|---------|-------------|------------|--------------------------|-----------------------|
| CADTIESC14CBAP | 601009         | Nylon, Stainless Steel 301 (EN 1.4310) | Black   | 355.6m<br>m | 4.32<br>mm | 0 °C Min                 | -20 to 85 °C          |
| CADTIESC8CBAP  | 601018         | Nylon, Stainless Steel 301 (EN 1.4310) | Black   | 203.2m<br>m | 4.32<br>mm | 0 °C Min                 | -20 to 85 °C          |
| CADTIESC8CNAP  | 601019         | Nylon, Stainless Steel 301 (EN 1.4310) | Natural | 203.2m<br>m | 4.32<br>mm | 0 °C Min                 | -20 to 85 °C          |
| CADTIESC11CBAP | 601000         | Nylon, Stainless Steel 301 (EN 1.4310) | Black   | 279.4m<br>m | 4.32<br>mm | 0 °C Min                 | -20 to 85 °C          |

| Catalog Number | Article Number | Material                               | Color   | Length (L) | Width (W) | Installation Temperature | Operating Temperature |
|----------------|----------------|----------------------------------------|---------|------------|-----------|--------------------------|-----------------------|
| CADTIESC11CNAP | 601001         | Nylon, Stainless Steel 301 (EN 1.4310) | Natural | 279.4m     | 4.32 mm   | 0 °C Min                 | -20 to 85 °C          |
| CADTIESC14CNAP | 601010         | Nylon, Stainless Steel 301 (EN 1.4310) | Natural | 355.6m     | 4.32 mm   | 0 °C Min                 | -20 to 85 °C          |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

