

Split Bottom Plates Stainless Steel, CBPS

A split bottom plate offers a flexible cabling solution and eliminates the need for individual cable glands. The protection degree is maintained by using a separate gasket.

FEATURES

Description: Fitted in place of the standard one piece bottom plate, allows direct cable entry. To achieve perfect sealing around the cables use the gasket kit BG01.

Material: AISI 304 / AISI 316L pre-grained stainless steel.

Bottom plates: 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 kit of two part bottom plate.

Thickness: 1.5mm
Finish: Brushed

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Enclosure Material	Material
CBPS1050	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0860	25mm	800mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0860-316	25mm	800mm	600mm	Stainless Steel	Stainless Steel 316
CBPS0850-316	25mm	800mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0650	25mm	600mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0640-316	25mm	600mm	400mm	Stainless Steel	Stainless Steel 316
CBPS1040	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0850	25mm	800mm	500mm	Stainless Steel	Stainless Steel 304
CBPS1040-316	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0840-316	25mm	800mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0840	25mm	800mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0650-316	25mm	600mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0640	25mm	600mm	400mm	Stainless Steel	Stainless Steel 304
CBPS1050-316	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 316
CBPS1060	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 304

Catalog Number	Height	Width	Depth	Enclosure Material	Material
CBPS0660-316	25mm	600mm	600mm	Stainless Steel	Stainless Steel 316
CBPS1060-316	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 316
CBPS0660	25mm	600mm	600mm	Stainless Steel	Stainless Steel 304

ADDITIONAL PRODUCT DETAILS

For enclosures 1200 mm & 1600 mm wide use 2 x 600 mm & 2 x 800 mm wide bottom plates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE