

# Universal Free-Stand Flat End Plate Mild Steel



Flat End plate is used to seal open side(s) of Universal Free-Stand Enclosures. The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated. Studs welded to the end plate eliminate bolt holes. Gasket and mounting hardware are furnished.

## FEATURES

Universal Free-Stand Flat End plate is used to seal open side(s) of nVent HOFFMAN Universal Free-Stand Enclosures.

The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated

Studs welded to the end plate eliminate bolt holes

Gasket and mounting hardware are furnished

**Color Code:** ANSI 61  
**Color:** Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Thickness |
|----------------|----------------|--------|-------|-------|-----------|
| AU7218FEP      | 38972          | 1832mm | 460mm | 7mm   | 1.98mm    |
| AU8424FEP      | 38974          | 2137mm | 613mm | 7mm   | 1.98mm    |
| AU8418FEP      | 38973          | 2137mm | 460mm | 7mm   | 1.98mm    |
| AU9024FEP      | 60456          | 2286mm | 613mm | 7mm   | 1.98mm    |
| AU9018FEP      | 60455          | 2286mm | 460mm | 7mm   | 1.98mm    |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**