

# Transversal Sliding Profiles, MTS



The fully equipped mounting plate can be slid easily into the enclosure from the side, which is essential since it is wider than the front opening. It is then fixed into place thanks to the U-profiles.

## FEATURES

Description: To be used when installing a wide mounting plate. Adjustable in depth in steps of 25 mm. Compatible with MTS01W rollers.

Pack quantity: 2 profiles with mounting accessories.

Material: 3 mm zinc plated steel.

**Thickness:** 3mm  
**Material:** Mild Steel  
**Finish:** Zinc Plated

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width  | Depth | Rollers Quantity | Enclosure Material |
|----------------|----------------|--------|--------|-------|------------------|--------------------|
| MTS800         | MTS800         | 52mm   | 800mm  | 68mm  | 3 min            | Mild Steel         |
| MTS1600        | MTS1600        | 52mm   | 1600mm | 68mm  | 7 min            | Mild Steel         |
| MTS1200        | MTS1200        | 52mm   | 1200mm | 68mm  | 5 min            | Mild Steel         |
| MTS500         | MTS500         | 52mm   | 500mm  | 68mm  | 2 min            | Mild Steel         |
| MTS1000        | MTS1000        | 52mm   | 1000mm | 68mm  | 4 min            | Mild Steel         |
| MTS600         | MTS600         | 52mm   | 600mm  | 68mm  | 3 min            | Mild Steel         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**