

# MTCA.4 Front Panel

AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

## FEATURES

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

|                        |                 |
|------------------------|-----------------|
| <b>Product Family:</b> | AdvancedMC      |
| <b>Accessory Type:</b> | Front panel     |
| <b>Type:</b>           | Front Panel     |
| <b>Product Type:</b>   | Front Panel     |
| <b>Material:</b>       | Stainless Steel |
| <b>EMC Shielding:</b>  | Yes             |



## SPECIFICATIONS

Table 1/2

| Catalog Number | Height  | Rack Width | Package Quantity | Mounting       | Gasket Type | Front Finish |
|----------------|---------|------------|------------------|----------------|-------------|--------------|
| 20849-214      | 170mm   | 2HP        | 1                | Screw-on Front | Textile EMC | Raw          |
| 20849-213      | 95mm    | 2HP        | 1                | Screw-on Front | Textile EMC | Raw          |
| 21850-102      | 84.68mm |            | 1                | Screw-on Front | Textile EMC | Raw          |
| 21850-103      | 84.68mm |            | 1                | Screw-on Front | Textile EMC | Raw          |

Table 2/2

| Catalog Number | Rear Finish | Depth | Width   |
|----------------|-------------|-------|---------|
| 20849-214      | Raw         | 0.6mm | 8.8mm   |
| 20849-213      | Raw         | 0.6mm | 8.8mm   |
| 21850-102      | Raw         | 1mm   | 18.96mm |
| 21850-103      | Raw         | 1mm   | 28.98mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**