

nVent CADDY Flexible Conduit Connector

CATALOG NUMBER

EZF1410

The nVent CADDY Flexible Conduit Connectors are a tool-free line of connectors built to accommodate a wide range of flexible conduit (1/4" to 10/2"). Designed to form an easy, secure, snap-in connection, the connectors also provide the option for a quick, damage-free removal by simply depressing the side tab and rotating the fitting to remove cables without harm. In addition, the unique three-prong design assists in keeping the cable secure to reduce the risk of accidental disconnection or pullout.

FEATURES

Innovative snap-in style design makes installing fitting to 1/2" box knockout fast and easy

Fitting can be easily removed by pressing tabs to release from box

Features ability to remove cables damage-free by simply twisting the fitting off cables

No tools required for installation

Offers insulated throat

Designed for AC, MCI-A, HCF steel and aluminum cable, flexible metal conduit steel and aluminum, MCI Cable, and continuous corrugated aluminum

Patented



PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Knockout Sizes: 1/2"

Diameter (Ø): 0.37"

Length (L): 1.54"

Width (W): 1"

Height (H): 0.86"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

