

nVent CADDY Flared Traditional Coupler

The nVent CADDY Flared Traditional Couplers are designed to reduce the number of steps required for installing conduit racks. The integrated flare helps align each piece of conduit to easily join and install prefabricated conduit racks. This design allows the coupler to simply slide over the conduit and have visual confirmation of correct insertion depth through the center viewport. Contractors can enjoy a significantly decreased amount of ladder time for overhead installations.

FEATURES

Designed for EMT conduit

Fast and simple installation

Center view slit in couplers center assists in conduit placement

Integrated flare feature is ideal for prefabrication



SPECIFICATIONS

Catalog Number	Length (L)	Width (W)	Height (H)	Depth (D)	Certifications
FC0050	1.795"	1.043"	1.499"	0.729"	
FC0075	2.185"	1.3"	1.756"	0.945"	UL, cUL
FC0100	2.72"	1.625"	2.075"	1.185"	UL, cUL
FC0125	3.325"	1.93"	2.39"	1.535"	UL, cUL
FC0150	3.872"	2.388"	2.848"	1.772"	UL, cUL
FC0200	4.187"	2.85"	3.31"	2.234"	cUL, UL
FC0250	4.828"	3.854"	4.385"	2.92"	cUL, UL
FC0300	4.999"	4.41"	4.941"	3.552"	cUL, UL
FC0350	5.479"	5.242"	5.773"	4.057"	cUL, UL
FC0400	5.675"	5.748"	6.279"	4.563"	UL, cUL

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

