

nVent CADDY Perfect Trim Adjustable Mud Ring

FEATURES

Two piece adjustable mud ring accommodates various thicknesses of drywall

Inner ring is removable which allows devices to be installed after drywall installation

Can be used with nVent CADDY Perfect Trim Protector Plate (sold separately) that snaps into inner ring to prevent damage during drywall installation

Can be used with nVent CADDY Perfect Trim Clip (sold separately) that snaps into inner ring to hold box bracket flush and rigid to drywall

Can be used with nVent CADDY Perfect Trim Extension Ring (sold separately) that attaches to inner ring for additional depths up to 2 1/4"

Finish: Pregalvanized
Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	Box Size	Gang	Drywall Thickness	A	B	Height (H)
PTDG411	4 11/16"	2	5/8" - 1 1/4"	4.68"	4.68"	0.620" - 1.45"
PTSG411	4 11/16"	1	5/8" - 1 1/4"	4.68"	4.68"	0.620" - 1.45"
PTDG4	4"	2	5/8" - 1 1/4"	4.1"	4.1"	0.620" - 1.45"
PTSG4	4"	1	5/8" - 1 1/4"	4.1"	4.1"	0.620" - 1.45"

Table 2/2

Catalog Number	Thickness (T)	Unit Weight
PTDG411	1/16"	0.54 lb
PTSG411	1/16"	0.56 lb
PTDG4	1/16"	0.45 lb
PTSG4	1/16"	0.46 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

