

Threaded Rod

FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

Yield Strength: 36000lbf/in²
Tensile Strength: 58000 lbf/in²
Finish: Electrogalvanized
Material: Steel

SPECIFICATIONS

Catalog Number	Rod Size (RS)	Length (L)	Static Load (F)
0502506EG	1/4"	6'	240lbf
0502510EG	1/4"	10'	240lbf
0503710EG	3/8"	10'	610lbf
0503706EG	3/8"	6'	600lbf
0505006EG	1/2"	6'	1130lbf
0505010EG	1/2"	10'	1130lbf
0506210EG	5/8"	10'	1810lbf
0506206EG	5/8"	6'	1810lbf
0507510EG	3/4"	10'	2710lbf
0507506EG	3/4"	6'	2710lbf
0508706EG	7/8"	6'	3770lbf
0508710EG	7/8"	10'	3770lbf

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

