

Wire Basket Tray, Round Wire

The nVent CADDY Wire Basket Tray, Round Wire is a continuous pathway solution to support high-performance cabling systems while providing an ideal foundation for datacom and electrical contractors.

FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fiber optic

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification

Material: Steel

SPECIFICATIONS

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT2X4PW	Pregalvanized	Pewter	2"	4	118"	8 lb
WBT2X6PW	Pregalvanized	Pewter	2"	6	118"	9 lb
WBT2X12PW	Pregalvanized	Pewter	2"	12	118"	14 lb
WBT2X8PW	Pregalvanized	Pewter	2"	8	118"	9.78 lb
WBT2X24PW	Pregalvanized	Pewter	2"	24	118"	24 lb
WBT2X18PW	Pregalvanized	Pewter	2"	18	118"	19 lb
WBT4X12PW	Pregalvanized	Pewter	4"	12	118"	18 lb
WBT4X18PW	Pregalvanized	Pewter	4"	18	118"	23 lb
WBT4X24PW	Pregalvanized	Pewter	4"	24	118"	29 lb
WBT4X6PW	Pregalvanized	Pewter	4"	6	118"	11 lb
WBT4X4PW	Pregalvanized	Pewter	4"	4	118"	10 lb
WBT4X8PW	Pregalvanized	Pewter	4"	8	118"	14 lb
WBT6X18PW	Pregalvanized	Pewter	6"	18	118"	25 lb

2" DEEP TRAY	
Tray Size	Splice Qty
2X4	2
2X6	3
2X8	3
2X12	3
2X16	4
2X18	4
2X20	4
2X22	5
2X24	5
2X26	6
2X28	6
2X30	6
2X32	7
2X34	7
2X36	8
2X38	8
2X40	9
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

4" DEEP TRAY	
Tray Size	Splice Qty
4X4	3
4X6	3
4X8	3
4X12	3
4X16	4
4X18	4
4X20	4
4X22	4
4X24	5
4X28	5
4X30	6
4X32	6
4X34	6
4X36	7
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

6" DEEP TRAY	
Tray Size	Splice Qty
6X8	3
6X12	3
6X16	3
6X18	4
6X20	4
6X22	4
6X24	4
6X26	5
6X28	5
6X30	5
6X32	6
6X34	6
6X36	7
These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above	

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

