

Door Mounting Profiles, MMDP



These mounting profiles will ensure that the enclosure's door does not bend and allows electrical components and other accessories to be fitted easily.

FEATURES

Description: To strengthen the door and provide further mounting possibilities. Mounted on the inside of the door onto M6 welded studs. Equipped with a 10 mm hole pattern. These door profiles cannot be used with the AFS enclosure range.

Material: 1.2 mm galvanized steel.

Dimension: 15 x 14 mm.

Pack quantity: 1 pair with mounting accessories.

Thickness: 18ga
Finish: Galvanized
Material: Mild Steel

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
MMDP050	MMDP050	17.24in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP120	MMDP120	44.8in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP040	MMDP040	13.31in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP140	MMDP140	52.68in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP060	MMDP060	21.18in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP070	MMDP070	25.12in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP080	MMDP080	29.06in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel
MMDP100	MMDP100	36.93in	0.59in	0.53in	Wall Mounted, Human Machine Interface	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE