

Easy Swap Adaptor Plenums for Air Conditioners



When existing air conditioners are damaged or have reached end-of-life, Easy Swap Adaptor Plenums provide a quick and easy means for attaching a new nVent HOFFMAN air conditioners to the cutout left on the enclosure.

INDUSTRY STANDARDS

Maintains NEMA Type 12 rating when properly installed on a Type 12 enclosure.

NEMA Type 12

IP 54

FEATURES

No modification of the enclosure required - designed to match the enclosure cut-out and mounting holes of the air conditioner being replaced

Plenum design allows for optimum air flow (vs. a flat plate that can block the air intake and air outtake left by the older air conditioner)

Gasket included

Color: Light Gray

Color Code: RAL 7035

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLM28G28	26294	NEMA Type 12	EasySwap	28.5in	17in	1.5in
PLM33N28	26296	NEMA Type 12	EasySwap	34.31in	12in	1.5in
PLRG52	19862	NEMA Type 12	EasySwap	61.13in	17.13in	1.5in
PLKG28	26582	NEMA Type 12	EasySwap	36.87in	19.13in	1.5in
PLCR23N21	36412	NEMA Type 12	EasySwap	23in	10in	1.5in
PLM36N36	26297	NEMA Type 12	EasySwap	38.75in	15in	1.5in
PLKG52	26581	NEMA Type 12	EasySwap	52.56in	19.13in	1.5in

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLRG57	26073	NEMA Type 12	EasySwap	61.13in	20.88in	1.5in
PLM28N17	26557	NEMA Type 12	EasySwap	28.5in	17in	1.5in
PL17N21SS	36417	NEMA Type 12	EasySwap	20.87in	12in	1.5in
PLRG28	21496	NEMA Type 12	EasySwap	37.4in	16.97in	1.5in
PLM52G52	26298	NEMA Type 12	EasySwap	52.56in	17.03in	1.5in
PLRN28	26068	NEMA Type 12	EasySwap	29in	11.5in	1.5in
PLR2N17	26067	NEMA Type 12	EasySwap	21.65in	12in	1.5in
PLHC52T53	26302	NEMA Type 12	EasySwap	52.85in	23in	1.5in
PLKTN17	26568	NEMA Type 12	EasySwap	19in	12in	1.5in
PLM13N17	26556	NEMA Type 12	EasySwap	17.65in	14.25in	1.5in
PLT29G28	26295	NEMA Type 12	EasySwap	28.5in	17in	1.5in
PLHC52G57	26301	NEMA Type 12	EasySwap	57.6in	22.97in	1.5in
PLKTN28	26505	NEMA Type 12	EasySwap	33.25in	12.25in	1.5in

Table 2/2

Catalog Number	Article Number	Protection Rating	Product Family	Height	Width	Depth
PLR1N17	26066	NEMA Type 12	EasySwap	21.65in	13in	1.5in
PLM13N16	36414	NEMA Type 12	EasySwap	17.65in	14.25in	2.62in
PLR2G28	26504	NEMA Type 12	EasySwap	37.4in	16.97in	1.5in
PLRN36	26538	NEMA Type 12	EasySwap	38in	15.75in	1.5in
PLPN36	26537	NEMA Type 12	EasySwap	36.5in	12in	1.5in
PL17N21	36416	NEMA Type 12	EasySwap	20.87in	12in	1.5in
PLCR23N21SS	36411	NEMA Type 12	EasySwap	23in	10in	1.5in

ADDITIONAL PRODUCT DETAILS

To quickly identify the correct air conditioner and plenum download the spec sheet from the Downloads tab or download the Easy Swap app from Apple App or Google play stores

Please contact Customer Service for support in finding an appropriate cross for older HOFFMAN/Mclean models not shown above.

Prior to ordering, ensure Adaptor Plenum dimensions do not exceed available space on the enclosure mounting surface.

ISC is a registered trademark of ISC Sales, Inc.

Kooltronic is a registered trademark of Kooltronic, Inc.

Pfannenbergl is a registered trademark of Pfannenbergl Incorporated

Rittal is a registered trademark of Rittal Corporation

Adaptor Plenums for Rittal are not suitable for replacing partial-recessed or fully-recessed mounted air conditioners.

Thermal Edge is a registered trademark of Thermal Edge, Inc.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE