

Front/Rear Plinths, PF

The front and rear plinth allows for cabling without any restrictions in accordance with the VDE 0113 standard. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each side for added strength.

Material: Corner pieces in 2 mm and panels in 1.5 mm mild steel.

Finish: RAL 7022 structured powder coating.

Pack quantity: 1 set of 4 corner pieces including covers. Front and rear panel (2 rear panels for 200 mm high plinths) with mounting accessories. Mounting accessories for side panels PS or transversal profiles PCP.

Mounting requirements: Add the side panels PS for a complete plinth. When combining enclosures it is recommended to add transversal panels PCP for cable duct support and extra rigidity.



Thickness: 16ga
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7022
Color: Umbra Gray

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
PF1080 	PF1080	3.94in	31.5in	2.46in	Free-Standing	Mild Steel
PF2140	PF2140	7.87in	55.04in	2.46in	Free-Standing	Mild Steel
PF2060	PF2060	7.87in	23.62in	2.46in	Free-Standing	Mild Steel

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
PF2080	PF2080	7.87in	31.5in	2.46in	Free-Standing	Mild Steel
PF1060	PF1060	3.94in	23.62in	2.46in	Free-Standing	Mild Steel
PF1120	PF1120	3.94in	47.24in	2.46in	Free-Standing	Mild Steel
PF2120 	PF2120	7.87in	47.24in	2.46in	Free-Standing	Mild Steel
PF1070	PF1070	3.94in	23.54in	2.46in	Free-Standing	Mild Steel
PF1090	PF1090	3.94in	35.43in	2.46in	Free-Standing	Mild Steel
PF2050	PF2050	7.87in	19.69in	2.46in	Free-Standing	Mild Steel
PF1040	PF1040	3.94in	15.75in	2.46in	Free-Standing	Mild Steel
PF2100	PF2100	7.87in	39.37in	2.46in	Free-Standing	Mild Steel
PF2070	PF2070	7.87in	31.42in	2.46in	Free-Standing	Mild Steel
PF1050	PF1050	3.94in	19.69in	2.46in	Free-Standing	Mild Steel
PF1140	PF1140	3.94in	15.67in	2.46in	Free-Standing	Mild Steel
PF2090	PF2090	7.87in	35.43in	2.46in	Free-Standing	Mild Steel
PF2040	PF2040	7.87in	15.75in	2.46in	Free-Standing	Mild Steel
PF1100	PF1100	3.94in	39.37in	2.46in	Free-Standing	Mild Steel

ADDITIONAL PRODUCT DETAILS

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE