

Glazed Doors, DNG



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

Thickness: 14ga
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Window Size	Product Family
DNG1406R5	DNG1406R5	54.41in	23.35in	0.66in	46.3 x 16.34in	Free-Standing
DNG1608R5	DNG1608R5	62.28in	31.22in	0.66in	54.17 x 24.21in	Free-Standing
DNG2008R5	DNG2008R5	78.03in	31.22in	0.66in	69.92 x 24.21in	Free-Standing
DNG2208R5	DNG2208R5	85.91in	31.22in	0.66in	77.8 x 24.21in	Free-Standing
DNG2210R5	DNG2210R5	85.91in	39.09in	0.66in	77.8 x 32.1in	Free-Standing

Catalog Number	Article Number	Height	Width	Depth	Window Size	Product Family
DNG1808R5	DNG1808R5	70.16in	31.22in	0.66in	62.05 x 24.21in	Free-Standing
DNG1606R5	DNG1606R5	62.28in	23.35in	0.66in	54.17 x 16.34in	Free-Standing
DNG1208R5	DNG1208R5	46.54in	31.22in	0.66in	38.43 x 24.21in	Free-Standing
DNG1408R5	DNG1408R5	54.41in	31.22in	0.66in	46.3 x 24.21in	Free-Standing
DNG2006R5	DNG2006R5	78.03in	23.35in	0.66in	69.92 x 16.34in	Free-Standing
DNG2206R5	DNG2206R5	85.91in	23.35in	0.66in	77.8 x 16.34in	Free-Standing
DNG1106R5	DNG1106R5	42.6in	23.35in	0.66in	34.49 x 16.34in	Free-Standing
DNG1806R5	DNG1806R5	70.16in	23.35in	0.66in	62.05 x 16.34in	Free-Standing
DNG1206R5	DNG1206R5	46.53in	23.35in	0.66in	38.42 x 16.34in	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE