

Open Frame Rack 2-Post



Designed for use in communication data centers and telecommunication rooms, 2-Post Open Frame Racks satisfy basic functional requirements for structuring cable. Racks are available in 3-inch or 6-inch column widths.

INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

FEATURES

Range of heights from 4 feet to 9 feet (24U to 58U) to match capacity requirements; 19-inch Rack Packages are 7-feet high

Side rails are tapped on both sides with 12-24UNC threads for quick installation

EIA Universal 5/8 inch - 5/8 inch - 1/2 inch vertical mounting hole pattern matches industry standards

RU markings on both front and back of uprights make it easier to mount equipment

Packed unassembled in individual cartons; assembly hardware is furnished for convenient storage and installation

Convenient rack and cable manager packages offered with either one or two 6-inch cable managers; includes one-piece hinged cover

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
EDR23FM45U	21669	84in	24.25in	15in	Aluminum	Powder Coated
EDR19FM45U 	21619	84in	20.25in	15in	Aluminum	Powder Coated
EVR23FM45U	22039	84in	24.25in	15in	Aluminum	Mill
EDR19FM45U6	25324	84in	20.28in	18in	Aluminum	Powder Coated
EVR23FM51U	22049	96in	24.25in	15in	Aluminum	Mill
EDR19FM45UCM1	14643	84in	27.5in	18in	Aluminum	Powder Coated
EDR19FM38U	21609	72in	20.25in	15in	Aluminum	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
EVR19FM58U	35319	108in	20.25in	15in	Aluminum	Mill
EDR19FM45UCM2 	14644	84in	34.75in	18in	Aluminum	Powder Coated
EVR19FM51U 	22029	96in	20.25in	15in	Aluminum	Mill
EDR19FM51U	21629	96in	20.25in	15in	Aluminum	Powder Coated
EDR19FM51U6	25325	96in	20.28in	18in	Aluminum	Powder Coated
EVR19FM45U	22019	84in	20.25in	15in	Aluminum	Mill
EDR19FM24U	21599	48in	20.25in	15in	Aluminum	Powder Coated
EDR23FM24U	21649	48in	24.25in	15in	Aluminum	Powder Coated
EWR19FM45U	36108	84in	20.25in	15in	Aluminum	Mill
EDR19FM58U	35309	108in	20.25in	15in	Aluminum	Powder Coated
EDR23FM38U	21659	72in	24.25in	15in	Aluminum	Powder Coated
EDR23FM51U	21679	96in	24.25in	15in	Aluminum	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE