


Outer Mounting Profiles, CLPO



A standard, off the shelf accessory compatible with nVent HOFFMAN's standard hole pattern, which simplifies procurement and installation.

FEATURES

Description: Universal profile for both depth and width fitting on the 25 mm DIN hole pattern on the enclosure frame. The 75 mm wide profile is equipped with three rows of holes of which one is turned 90°. This makes it possible to mount the CLPO profiles in both directions. The CLPO increases the useful space by 25 mm.

Material: 1.5 mm zinc plated steel.

Pack quantity: 4 profiles.

Finish: Galvanized

Material: Mild Steel

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Load Rating	Thickness
CLPO1200	CLPO1200	2.91in	1.69in	43.74in	1200N	0.06in
CLPO500	CLPO500	2.91in	1.69in	16.18in	2400N	0.06in
CLPO600	CLPO600	2.91in	1.69in	20.12in	2400N	0.06in
CLPO400	CLPO400	2.91in	1.69in	12.24in	2400N	0.06in
CLPO800	CLPO800	2.91in	1.69in	27.99in	1800N	0.06in
CLPO1000	CLPO1000	2.91in	1.69in	35.87in	1400N	0.06in
CLPO300		2.91in	1.69in	8.31in	2400N	16in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE