

Panels for Free-Stand with Mounting Channel One-Door

Panel for Free-Stand Single- and Dual-Access One-Door Enclosures with Mounting Channel. Panels can be positioned anywhere along horizontal mounting channels (see dimension drawing Sections B-B for limitations). Half-length panels can be located in the upper or lower portion of the enclosure.

FEATURES

Available in Full-Length and Half-Length

Plated mounting hardware is provided

Material: Mild Steel

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A90P24F2	23510	39.88in	20in	Powder Coated	White	12ga
A72P30F2G	15003	30.88in	26in	Galvanized		12ga
A60P24F1	21260	48in	20in	Powder Coated	White	12ga
A72P24F1G	14998	60in	20in	Galvanized		12ga
A60P24F2	21270	24.88in	20in	Powder Coated	White	12ga
A72P24F1	23320	60in	20in	Powder Coated	White	12ga
A90P36F1G	15006	78in	32in	Galvanized		12ga
A72P36F1G	15004	60in	32in	Galvanized		12ga
A72P24F2	23330	30.88in	20in	Powder Coated	White	12ga
A72P24F2G	15001	30.88in	20in	Galvanized		12ga
A72P36F2G	15005	30.88in	32in	Galvanized		12ga
A90P36F2G	15007	39.88in	32in	Galvanized		12ga
A90P36F2	23390	39.88in	32in	Powder Coated	White	12ga
A72P36F1 	23360	60in	32in	Powder Coated	White	12ga
A90P24F1	23480	78in	20in	Powder Coated	White	12ga
A90P24F2G	15011	39.88in	20in	Galvanized		12ga

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72P36F2	23370	30.88in	32in	Powder Coated	White	12ga
A60P36F1G	14996	48in	32in	Galvanized		12ga
A60P36F2	21290	24.88in	32in	Powder Coated	White	12ga
A60P36F2G	14997	24.88in	32in	Galvanized		12ga

Table 2/2

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A60P36F1	21280	48in	32in	Powder Coated	White	12ga
A90P24F1G	15008	78in	20in	Galvanized		12ga
A72P30F2	23350	30.88in	26in	Powder Coated	White	12ga
A72P30F1	23340	60in	26in	Powder Coated	White	12ga
A90P36F1 	23380	78in	32in	Powder Coated	White	12ga
A60P24F1G	14994	48in	20in	Galvanized		12ga
A60P24F2G	14995	24.88in	20in	Galvanized		12ga
A72P30F1G	15002	60in	26in	Galvanized		12ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE