

Side Doors, DNS



A side door mounted on an enclosure allows easy access to the rear part of components mounted in the front when access from the back is not possible.

FEATURES

Description: Instead of the side panel SPM. For easy access to the equipment inside the enclosure or when enclosures are mounted rear to rear. Equipped with standard double-bit 3 mm lock which makes all lock options possible. Door frame optional.

Material: 2 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 10.

Pack quantity: 1 door including mounting frame.

Thickness: 14ga
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
DNS2005R5	DNS2005R5	78.03in	19.41in	2.01in	Free-Standing	Mild Steel
DNS1806R5	DNS1806R5	70.16in	23.35in	2.01in	Free-Standing	Mild Steel
DNS2006R5	DNS2006R5	78.03in	23.35in	2.01in	Free-Standing	Mild Steel
DNS1805R5	DNS1805R5	70.16in	19.41in	2.01in	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE