

Side Plinths Mild Steel, PS



The extra space created by the plinth is closed off by using these panels in order to restrict access to this area.

FEATURES

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

Thickness: 16ga
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7022
Color: Umbra Gray

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Product Family	Enclosure Material
PS2100	PS2100	7.87in	39.37in	1.04in	Free-Standing	Mild Steel
PS1060	PS1060	3.94in	23.62in	1.04in	Free-Standing	Mild Steel
PS2080	PS2080	7.87in	31.5in	1.04in	Free-Standing	Mild Steel
PS1040	PS1040	3.94in	15.75in	1.04in	Free-Standing	Mild Steel
PS2050	PS2050	7.87in	19.69in	1.04in	Free-Standing	Mild Steel
PS1080	PS1080	3.94in	31.5in	1.04in	Free-Standing	Mild Steel
PS2030	PS2030	7.87in	11.81in	1.04in	Free-Standing	Mild Steel
PS1100	PS1100	3.94in	39.37in	1.04in	Free-Standing	Mild Steel
PS2040	PS2040	7.87in	15.75in	1.04in	Free-Standing	Mild Steel
PS2060	PS2060	7.87in	23.62in	1.04in	Free-Standing	Mild Steel
PS1050	PS1050	3.94in	19.69in	1.04in	Free-Standing	Mild Steel
PS1030	PS1030	3.94in	11.81in	1.04in	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE