

Thermoelectric Coolers Indoor/Outdoor



Thermoelectric Coolers minimize downtime and component loss by removing heat around critical components within an enclosure. These compact, low-profile coolers using the Peltier effect allow for cooling of small indoor and outdoor enclosures. No condensers, compressors or filters are required making it a reliable solution for demanding low-maintenance environments and low noise.

Operates on the Peltier effect for cooling or heating

INDUSTRY STANDARDS

UR, cUR Recognized; Type 12, 3R, 4, 4X; File No. SA6453

CE

IP 65

FEATURES

Operates on the Peltier effect for cooling or heating

Contains no refrigerant, making it earth friendly

Filterless design reduces maintenance requirements

Compressor-free air conditioning for demanding indoor and outdoor applications

Prewired with simple terminal block for easy wiring connections

Shrouded and unshrouded models included in standard packages

Operating temperature range -40 C (-40 F) to 55 C (131 F)

Partial recess mount

DC Powered operation for 24V and 48V applications

Low profile design allows for mounting vertically and horizontally on any enclosure to avoid interference with internal components

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Btu/h
TE162048020	21064	15.75in	7.09in	7.25in	48V	567Btu/h
TE090624020	21065	9.06in	4.84in	6.91in	24V	178Btu/h
TE090624010	21074	9.29in	5.02in	6.94in	24V	178Btu/h

Catalog Number	Article Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Btu/h
TE121024011	21072	12in	6.18in	7.43in	24V	321Btu/h
TE121024020	21066	11.81in	6.02in	7.4in	24V	321Btu/h
TE121024010 	21075	12in	6.18in	7.43in	24V	321Btu/h
TE121048010	21071	12in	6.18in	7.43in	48V	321Btu/h
TE121048020	20812	11.81in	6.02in	7.4in	48V	321Btu/h
TE162024011 	21067	15.93in	7.35in	7.27in	24V	567Btu/h
TE162024010 	21077	15.93in	7.35in	7.27in	24V	567Btu/h
TE162024020	21068	15.75in	7.09in	7.25in	24V	567Btu/h
TE090624011 	21076	9.29in	5.02in	6.94in	24V	178Btu/h
TE162048010	21073	15.93in	7.35in	7.27in	48V	567Btu/h

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE