

Universal Free-Stand Formed End Plate Mild Steel



End plate is used to seal open side(s) of Universal Free-stand Enclosures. The 2.50-inch deep End Plate allows extra wiring space and is Type 4, 12, 3R and IP66 rated. Gasket and mounting bolts are included.

FEATURES

Universal Free-Stand Formed End plate is used to seal open side(s) of nVent HOFFMAN Universal Free-stand Enclosures.

The 2.50-inch deep End Plate allows extra wiring space and is Type 4, 12, 3R and IP66 rated

Gasket and mounting bolts are included

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Thickness
AU8424EPT	38987	84.13in	24.13in	2.5in	14ga
AU9018EPT	60453	90.13in	18.11in	2.5in	14ga
AU8418EPT 	38986	84.13in	18.11in	2.5in	14ga
AU7218EPT	38983	72.13in	18.11in	2.5in	14ga
AU9024EPT	60454	90.13in	24.13in	2.5in	14ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE