

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.

FEATURES

Axial 119 mm DC fan, with plug for connection cable



SPECIFICATIONS

Catalog Number	Works With	Voltage DC	Noise Level	Power	Package Quantity
60713-600	19" Fan Trays	12V	39dB(A)	8W	1
20713-242	19" Fan Trays	48V	42dB(A)	8W	1
20713-241	19" Fan Trays	12V	42dB(A)	8W	1
20713-240	19" Fan Trays	24V	42dB(A)	8W	1
20713-172	19" Fan Trays	24V	50.5dB(A)	7W	1

ADDITIONAL PRODUCT DETAILS

Please order connection cable and protective grille separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE